

# **Owner's Manual**

## **USB-C Adapter, Dual Display - 4K HDMI with Multi-Stream Transport**

**Model: U444-06N-2H-MST**

*USB Type-C® and USB-C® are registered trademarks  
of USB Implementers Forum.*

**Este manual está disponible en español en la página  
de Tripp Lite: [tripplite.com](http://tripplite.com)**

**Ce manuel est disponible en français sur le site Web  
de Tripp Lite : [tripplite.com](http://tripplite.com)**

**Русскоязычная версия настоящего руководства  
представлена на веб-сайте компании Tripp Lite по  
адресу: [tripplite.com](http://tripplite.com)**

**WARRANTY REGISTRATION**  
Register your product today and be automatically entered to  
win an ISOBAR® surge protector in our monthly drawing!  
**[tripplite.com/warranty](http://tripplite.com/warranty)**



**1111 W. 35th Street, Chicago, IL 60609 USA**  
**[tripplite.com/support](http://tripplite.com/support)**

Copyright © 2021 Tripp Lite. All rights reserved.  
All trademarks are the property of their owners.



## Product Features

- Connects 2 HDMI displays to the USB-C or Thunderbolt 3 port on your laptop, tablet, MacBook or Chromebook
- Supports USB DisplayPort Alternate Mode, allowing you to output 4K video and digital audio without installing special software drivers
- Supports Ultra HD video resolutions up to 3840 x 2160 (4K x 2K) at 30 Hz
- Supports 36-bit Deep Color (12 bits per channel) and 7.1-channel surround sound
- SST and MST functions transmit the same source content to two displays or different content to each display
- Slim design is perfect for travel and easy to carry in a pocket, briefcase or laptop bag for connecting on the go
- Plug-and-play operation with no software required for easy, immediate installation

## **Package Contents**

- U444-06N-2H-MST
- Owner's Manual

## **System Requirements**

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device(s) with HDMI input
- Windows required for Multi-Stream Transport

## **Optional Accessories**

- P568-Series High-Speed HDMI Cables
- P569-XXX-CERT Premium High-Speed HDMI Cables with Gripping Connectors

## Installation

- 1.** Connect the USB Type-C connector on the adapter to the USB Type-C port on your laptop, tablet, MacBook or Chromebook.
- 2.** Connect the HDMI ports on the adapter to monitors using HDMI cables (such as Tripp Lite's P568-Series HDMI cables).
- 3.** The video images will appear on the add-on monitors. Customize how video is displayed on the add-on monitors using your device's display settings.

**Note:** *macOS does not support MST for NVIDIA and Intel graphics processors, limiting video display on the connected monitors to mirror mode.*

## Specifications

<b>Connectors</b>	
Input	USB-C (Male)
Output	2x HDMI (Female)
<b>Video</b>	
Maximum Resolution	3840 x 2160 @ 30 Hz
Color Depth	36-bit Deep Color (12 bits per channel)
<b>Environmental</b>	
Operating Temperature	32° to 113°F (0° to 45°C)
Storage Temperature	14° to 158°F (-10° to 70°C)
Operating Humidity	10% to 85%, Non-Condensing
Storage Humidity	5% to 90%, Non-Condensing

## Warranty and Product Registration

### 3-Year Limited Warranty

TRIPP LITE warrants its products to be free from defects in materials and workmanship for a period of three (3) years from the date of initial purchase. TRIPP LITE's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from TRIPP LITE or an authorized TRIPP LITE service center. Products must be returned to TRIPP LITE or an authorized TRIPP LITE service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, TRIPP LITE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL TRIPP LITE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, TRIPP LITE is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

# Warranty and Product Registration

## Product Registration

Visit [www.tripplite.com/warranty](http://www.tripplite.com/warranty) today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!\*

\* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

## FCC Notice, Class B

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

**Note:** This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

## Warranty and Product Registration

Any changes or modifications to this equipment not expressly approved by Tripp Lite could void the user's authority to operate this equipment.

### WEEE Compliance Information for Tripp Lite Customers and Recyclers (European Union)



Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Tripp Lite they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



Manufacturing  
Excellence.

1111 W. 35th Street, Chicago, IL 60609 USA  
[triplite.com/support](http://triplite.com/support)