

Owner's Manual

HDMI to Composite Video with Audio Converter

Model: P130-000-COMP

Este manual esta disponible en español en la página de Tripp Lite:
www.tripplite.com/support

Ce manuel est disponible en français sur le site Web de Tripp Lite :
www.tripplite.com/support

Русскоязычная версия настоящего руководства
представлена на веб-сайте компании Tripp Lite по адресу:
www.tripplite.com/support

PROTECT YOUR INVESTMENT!

Register your product for quicker service and ultimate peace of mind.
You could also win an ISOBAR6ULTRA surge protector—a \$100 value!

www.tripplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA • www.tripplite.com/support

Copyright © 2018 Tripp Lite. All rights reserved.

Product Features

- Converts an HDMI audio/video signal for use with composite video displays
- Supports uncompressed 2-channel stereo audio
- Allows you to enjoy high-quality image and sound when watching movies or playing games on monitors and projectors equipped with composite video ports
- Converts an HDMI source for display in NTSC or PAL
- Supports maximum output resolutions up to 480i (NTSC) or 576i (PAL)
- Supports maximum HDMI input resolutions up to 1080p
- International power supply includes NEMA 1-15P (North America), CEE 7/16 Schuko (Europe), BS1363 (UK) and AS/NZS 3112 (Australia) plugs

Package Includes

- P130-000-COMP
- External Power Supply*
(Input: 100-240V, 50/60 Hz, 0.3A; Output: 5V 1A)
- Mounting Hardware
- Owner's Manual

*Includes NEMA 1-15P (North America), CEE 7/16 Schuko (Europe), BS1363 (UK) and AS/NZS 3112 (Australia) plugs

Optional Accessories

- P568-Series High-Speed HDMI Cables
- A004-006 Composite Video Cable, 6 ft.
- A050-006 R/L Stereo Audio Cable, 6 ft.

System Requirements

- HDMI-enabled audio/video source
- Composite video-enabled display device with R/L stereo audio

Installation

Note: Before installation, make sure all devices and components are powered off.

- 1. Optional:** Mount the unit to a wall or other surface using the included mounting hardware.
- 2.** Connect the HDMI port on your source to the input port on the unit using an HDMI audio/video cable.
- 3.** Connect the composite video output port on the unit to the port on your display using a composite video cable.
- 4.** Connect RCA stereo audio cables from the output ports on the unit to the audio device.
- 5.** Connect the power supply to the unit and plug it into a Tripp Lite Surge Protector, Power Distribution Unit (PDU) or Uninterruptible Power Supply (UPS).
- 6.** Power on the connected devices.
- 7.** You can toggle between NTSC and PAL video modes using the switch on the unit.

Specification	Value
Input Port	HDMI, Female
Output Ports	1 x RCA Composite Video, Female 2 x RCA Stereo Audio, Female
Operating Temperature	32° to 113° F / 0° to 45° C
Storage Temperature	14° to 158° F / -10° to 70° C
Operating Humidity	10% to 85% RH, Non-Condensing
Storage Humidity	5% to 90% RH, Non-Condensing
External Power Supply	Input: 100-240V, 50/60 Hz, 0.3A; Output: 5V 1A
Power Consumption	5W Max.
Maximum Input Resolutions	1080p
Maximum Output Resolutions	480i (NTSC) and 576i (PAL)
Unit Dimension (H x W x D)	0.98 x 4.02 x 3.94 in. / 25 x 100 x 100 mm
Unit Weight	1.36 lb. / 0.6 kg

Warranty and Product Registration

2-YEAR LIMITED WARRANTY

TRIPP LITE warrants its products to be free from defects in materials and workmanship for a period of two (2) years from the date of initial purchase. TRIPP LITE's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from TRIPP LITE or an authorized TRIPP LITE service center. Products must be returned to TRIPP LITE or an authorized TRIPP LITE service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, TRIPP LITE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL TRIPP LITE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, TRIPP LITE is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

PRODUCT REGISTRATION

Visit www.tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

FCC Notice, Class B


This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Any changes or modifications to this equipment not expressly approved by Tripp Lite could void the user's authority to operate this equipment.

WEEE Compliance Information for Tripp Lite Customers and Recyclers (European Union)

 Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Tripp Lite they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended. Do not use this equipment in the presence of a flammable anesthetic mixture with air, oxygen or nitrous oxide.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



1111 W. 35th Street,
Chicago, IL 60609 USA
www.tripplite.com/support