

# Owner's Manual

## M.2 NGFF SSD to 2.5" SATA Open-Frame Housing Adapter

Model: P960-001-M2-NE

Este manual esta disponible en español en la página de  
Tripp Lite: [www.tripplite.com/support](http://www.tripplite.com/support)

Ce manuel est disponible en français sur le site Web de  
Tripp Lite : [www.tripplite.com/support](http://www.tripplite.com/support)

Русскоязычная версия настоящего руководства представлена на  
веб-сайте компании Tripp Lite по адресу: [www.tripplite.com/support](http://www.tripplite.com/support)

### WARRANTY REGISTRATION

Register your product today and be automatically entered to win an  
ISOBAR surge protector in our monthly drawing!

[www.tripplite.com/warranty](http://www.tripplite.com/warranty)



1111 W. 35th Street, Chicago, IL 60609 USA • [www.tripplite.com/support](http://www.tripplite.com/support)

Copyright © 2019 Tripp Lite. All rights reserved.

## Product Features

- Convert an M.2 NGFF SSD into a 7 mm high, 2.5 in. SATA SSD
- Open-frame housing helps maximize heat dissipation
- Supports full-length M.2 NGFF SSD B/B+M-key (2242, 2260, 2280)
- Supports SATA revisions I/II/III (1.5/3/6 Gbps)
- Plug-and-play—no software or drivers required

## System Requirements

- M.2 NGFF SATA Drive (supports B & B+M Key SATA drives—PCIe drives are not supported)
- SATA Host Device

## Package Contents

- P960-001-M2-NE
- Mounting Hardware
- Screwdriver
- Owner's Manual

# Installation

## Notes:

- *SSD drives are sensitive to static electricity. To avoid the risk of data loss, the SSD must be handled properly. Always handle your SSD with caution by wearing an anti-static strap (such as Tripp Lite's P999-000) when transporting it, or by touching a grounded metal surface to discharge yourself of static electricity prior to picking up the drive.*
  - *If your drive has not been formatted, you will first need to format it using your computer's Disk Management utility in order to copy and access files.*
  - *Prior to unplugging the open frame adapter, make sure to properly eject the drive from your computer to avoid any potential data loss.*
- 1.** Depending on the size of your drive, insert the included nut into the circular slot at the 42 mm, 60 mm or 80 mm lines.
  - 2.** Connect your drive by inserting it into the M.2 NGFF connector. Keep the drive at a low angle to minimize stress on the connector.
  - 3.** Using the included screw and screwdriver, secure the drive by screwing it into the nut.
  - 4.** Connect the unit to the SATA port on your computer. Your drive is now ready for use.

# Warranty and Product Registration

## 1-Year Limited Warranty

Tripp Lite warrants its products to be free from defects in materials and workmanship for a period of one (1) year from the date of initial purchase. Tripp Lite's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from Tripp Lite or an authorized Tripp Lite service center. Products must be returned to Tripp Lite or an authorized Tripp Lite service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

# Warranty and Product Registration

EXCEPT AS PROVIDED HEREIN, Tripp Lite MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL Tripp Lite BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, Tripp Lite is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

## Product Registration

Visit [www.tripplite.com/warranty](http://www.tripplite.com/warranty) today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!\*

\* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

## WEEE Compliance Information for Tripp Lite Customers and Recyclers (European Union)



Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Tripp Lite they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



1111 W. 35th Street, Chicago, IL 60609 USA • [www.tripplite.com/support](http://www.tripplite.com/support)