

Quick Start Guide

Crimping Tool with Cable Stripper for Pass-Through RJ45 Plugs

Model: T100-PT1

Package Includes

- T100-PT1
- Quick Start Guide

Este guía esta disponible en español en la página de
Tripp Lite: triplite.com/support

Ce guide est disponible en français sur le site Web de
Tripp Lite : triplite.com/support

Русскоязычная версия настоящего краткого
руководства представлена на веб-сайте компании
Tripp Lite по адресу: triplite.com/support

Dieses Handbuch ist in deutscher Sprache auf der
Tripp Lite-Website verfügbar: triplite.com/support

WARRANTY REGISTRATION

Register your product today and be automatically entered to
win an ISOBAR® surge protector in our monthly drawing!

triplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA • triplite.com/support

Copyright © 2020 Tripp Lite. All rights reserved.

Optional Accessories

- N020-Series Cat5e Stranded Conductor Bulk Cable – 1,000 ft.
- N022-01K-GY Cat5e Solid Conductor Bulk Cable, Gray – 1,000 ft.
- N024-01K Cat5e Solid Conductor Plenum-Rated Bulk Cable, Gray – 1,000 ft.
- N028-01K-GY Cat5e Solid Conductor Outdoor-Rated Bulk Cable, Gray – 1,000 ft.
- N030-010 Cat5e RJ45 Plugs for Solid / Stranded Conductor Cable – 10 Pack
- N030-100 Cat5e RJ45 Plugs for Solid / Stranded Conductor Cable – 100 Pack
- N031-050 Cat5e RJ45 Plugs for Stranded Conductor Cable – 100 Pack
- N222-Series Cat6 Solid Conductor Plenum-Rated Bulk Cable, Gray – 1,000 ft.
- N230-100 Cat6 RJ45 Plugs for Solid / Stranded Conductor Cable – 100 Pack

Opening / Closing the Tool

To open the tool handles, simply squeeze them together and release. To lock the handles in place, squeeze them together and push the lock button.

Stripping Round Cable

Insert the cable into the slot located in front of the lower scoring cable. Squeeze the tool's handles and rotate the tool around the cable to score the jacket. Pull off the jacket.

Cutting Cable

One side of the tool is a single blade for cutting cable. Insert the cable to the desired length into the slot underneath the blade. Then cut the cable by squeezing the handles together until the cable cleanly separates.

Crimping Connectors

Once the jacket has been stripped from the cable, insert the cable wires into an appropriate plug. Follow by inserting the plug into the tool's corresponding 6-Pin or 8-Pin slot, then squeeze the handles to crimp.

Assembly Diagram

- 1** Put the Ethernet cable into stripper tool



- 2** Cut the skin and strip the jacket off of the cable



- 3** Separate the wires



- 4** Cut off the foil or film



- 5** Keep the wires neat



- 6** Cut the wires at an oblique angle



- 7** Insert the core wire into the RJ45 Plug



- 8** Crimp plug



- 9** Complete



RJ45 COLOR CODING SYSTEM	
	1. White Green 2. Green 3. White Orange 4. Blue 5. White Blue 6. Orange 7. White Brown 8. Brown
	1. White Orange 2. Orange 3. White Green 4. Blue 5. White Blue 6. Green 7. White Brown 8. Brown

Warranty and Product Registration

3-Year Limited Warranty

TRIPP LITE warrants its products to be free from defects in materials and workmanship for a period of three (3) years from the date of initial purchase. TRIPP LITE's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from TRIPP LITE or an authorized TRIPP LITE service center. Products must be returned to TRIPP LITE or an authorized TRIPP LITE service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, TRIPP LITE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL TRIPP LITE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, TRIPP LITE is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

PRODUCT REGISTRATION

Visit triplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.



1111 W. 35th Street, Chicago, IL 60609 USA • triplite.com/support