

# Quick Start Guide

## USB-C to Stereo Audio Adapter

Model: U437-001

Este manual está disponible en español en la página de Tripp Lite: [tripplite.com](http://tripplite.com)

Ce manuel est disponible en français sur le site Web de Tripp Lite : [tripplite.com](http://tripplite.com)

Русскоязычная версия настоящего руководства представлена на веб-сайте компании Tripp Lite по адресу: [tripplite.com](http://tripplite.com)

Dieses Handbuch ist in deutscher Sprache auf der Tripp Lite-Website verfügbar: [tripplite.com](http://tripplite.com)

### WARRANTY REGISTRATION

Register your product today and be automatically entered to win an ISOBAR® surge protector in our monthly drawing!

[tripplite.com/warranty](http://tripplite.com/warranty)



1111 W. 35th Street, Chicago, IL 60609 USA  
[tripplite.com/support](http://tripplite.com/support)

Copyright © 2021 Tripp Lite. All rights reserved.  
USB Type-C® and USB-C® are registered trademarks of  
USB Implementers Forum.

## Product Features

- Adds a 3.5 mm stereo audio headphone port to a USB-C device that does not have a functioning one
- 24-bit digital-to-analog converter (DAC) supports 96 kHz sample rate
- Slim design fits easily into pocket, purse, backpack or laptop bag
- Plug-and-play operation with no software required for easy, immediate installation
- Compatible with Android™, Windows® and macOS®, including iPads with a USB-C port

## Product Features

- U437-001 USB-C to Stereo Audio Adapter
- Quick Start Guide

## Operation

- 1.** Connect the adapter's USB-C connector to the USB-C port on your smartphone, tablet, laptop or computer.
- 2.** Connect a set of headphones to the adapter's 3.5 mm audio jack.

## Specifications

| Connectors                  |                                   |
|-----------------------------|-----------------------------------|
| USB (Input)                 | USB Type-C (Male)                 |
| Audio (Output)              | 3.5 mm (Female)                   |
| Audio                       |                                   |
| Sampling Frequency          | 96 kHz, 24 Bit                    |
| Environmental               |                                   |
| Operating Temperature Range | -4° to 122°F / -20°C to 50°C      |
| Storage Temperature Range   | -4° to 158°F / -20°C to 70°C      |
| Relative Humidity Range     | 20% to 85% RH<br>(Non-Condensing) |
| Power                       | Bus-Powered                       |
| Physical                    |                                   |
| Cable Length                | 5.1 in. / 13 cm                   |

## Warranty and Product Registration

### 1-Year Limited Warranty

Seller warrants this product, if used in accordance with all applicable instructions, to be free from original defects in material and workmanship for a period of one (1) year from the date of initial purchase. If the product should prove defective in material or workmanship within that period, Seller will repair or replace the product, at its sole discretion.

THIS WARRANTY DOES NOT APPLY TO NORMAL WEAR OR TO DAMAGE RESULTING FROM ACCIDENT, MISUSE, ABUSE OR NEGLIGENCE. SELLER MAKES NO EXPRESS WARRANTIES OTHER THAN THE WARRANTY EXPRESSLY SET FORTH HEREIN. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ALL IMPLIED WARRANTIES, INCLUDING ALL WARRANTIES OF MERCHANTABILITY OR FITNESS, ARE LIMITED IN DURATION TO THE WARRANTY PERIOD SET FORTH ABOVE; AND THIS WARRANTY EXPRESSLY EXCLUDES ALL INCIDENTAL AND

## Warranty and Product Registration

**CONSEQUENTIAL DAMAGES.** (Some states do not allow limitations on how long an implied warranty lasts, and some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitations or exclusions may not apply to you. This warranty gives you specific legal rights, and you may have other rights which vary from jurisdiction to jurisdiction.)

**WARNING:** The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

### Product Registration

Visit [triplite.com/warranty](http://triplite.com/warranty) today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!\*

\*No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

### WEEE Compliance Information for Tripp Lite Customers and Recyclers (European Union)

Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Tripp Lite, they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.



1111 W. 35th Street, Chicago, IL 60609 USA  
[triplite.com/support](http://triplite.com/support)